## All technical data refer to the measure mm

**DIN 965** similar to ISO 7046

## **Countersunk bolts**

Hexalobular / Torx

Steel 4.8 | zinc-plated | Cr(VI)-free | Metric thread

Further information: DIN standard has been withdrawn

Diameter	a	b	d <sub>1</sub>	$d_2$	k	r	Pitch	Tool
(d)	max.	nominal size	nominal size	nominal size	max.	max.	(P)	size
M3	1	19	M3	5.6	1.65	0.8	0.5	T10

Length (I)					
nominal size	min.	max.			
4	3.75	4.25			

Diameter	Length (I)		
(d)	4		
M3			

 $\bullet$  Combinations available in the eShop | Other sizes on request