
DIN 976 A

Threaded rods

Form A: thread end without tip | length: 1 m

Steel 8.8 | hot-dip galvanised | Cr(VI)-free | Metric thread





Diameter	Pitch	Length (I)		
(d)	(P)	nominal size	min.	max.
M10	1.50	1,000	995.5	1,004.5
M12	1.75	1,000	995.5	1,004.5
M16	2.00	1,000	995.5	1,004.5
M20	2.50	1,000	995.5	1,004.5
M24	3.00	1,000	995.5	1,004.5
M27	3.00	1,000	995.5	1,004.5
M30	3.50	1,000	995.5	1,004.5
M36	4.00	1,000	995.5	1,004.5