

E 5152

EJOT Altracs® plus-screws

Button head | torx plus /autosert drive

Steel 10 | zinc-plated | Cr(VI)-free | Self-tapping thread

Further information: For further information and CAD-files please follow the link to the EJOT-homepage:

<http://www.ejot.com/industry>

Diameter (d)	d ₁ nominal size	r max.	Pitch (P)	t		Tool size
				max.	min.	
3	3	0.4	0.5	1.3	1.0	T10 (2,8)
4	4	0.5	0.7	1.8	1.4	T20 (3,95)
5	5	0.5	0.8	2.0	1.6	T25 (4,5)

Length (l)	
nominal size	
	8
	10
	12

Diameter (d)	Length (l)		
	8	10	12
3	●	●	●
4	●		
5			●

• Combinations available in the eShop | Other sizes on request

All technical data refer to the measure mm

