

E 5154

EJOT Altracs® plus-screws

Button head | torx plus /autosert drive

Steel 10 | zinc-plated | Cr(VI)-free | Self-tapping thread

Further information: For further information and CAD-files please follow the link to the EJOT-homepage:

<http://www.ejot.com/industry>

Diameter (d)	c nominal size	d ₁ nominal size	r nominal size	Pitch (P)	t		Tool size
					max.	min.	
3	0.55	3	0.8	0.5	1.05	0.8	10 IP

Length (l) nominal size
16

Diameter (d)	Length (l)
3	16 ●

- Combinations available in the eShop | Other sizes on request

All technical data refer to the measure mm

