

**E 5452**

**EJOT®-Delta PT-screws**

Raised countersunk head with pressed-on washer | torx plus /autosert drive

Steel 10 | zinc-plated | Cr(VI)-free | Self-tapping thread

Further information: For further information and CAD-files please follow the link to the EJOT-homepage:

<http://www.ejot.com/industry>

Diameter (d)	d <sub>1</sub> nominal size	r max.	Pitch (P)	t		Tool size
				max.	min.	
3	3	0.5	1.12	1.3	1.0	T10 (2,8)
6	6	0.8	2.14	2.4	1.9	T30 (5,6)

Length (l) nominal size
40

Diameter (d)	Length (l)	
	12	40
3	●	
6		●

• Combinations available in the eShop | Other sizes on request

All technical data refer to the measure mm

