## Brass | Type 1431 | Plus | flange


## Advantages:

- Suitable for thermoplastic parts
- High-strength and torsion-proof threads
- Chipless installation
- Special version available with external left-hand thread for improved reverse locking

## Note:

Also available without flange on request.





Diameter	Article number	d <sub>3</sub>	Length (I)		а	l <sub>2</sub>	Outer	L	
(d)		nominal size	nominal size	S	min.		diameter (d2)	min.	
M5	14310050114	11.5	11.4	4	5.5	1.4	9.12	10.4	
M6	14310060134	13	13.4	5	6.0	1.4	10.67	12.0	
M8	14310080174	18	17.4	6.5	7.0	1.4	13.76	16.0	

communication of its content only permitted with express consert.