# All technical data refer to the measure mm

# RIVKLE® M2007 Kit

RIVKLE® kit including RIVKLE® M2007 manual setting tool

### **Delivery scope:**

- 1 RIVKLE® M2007 hand-held setting tool
- 3 threaded mandrels and 3 anvils (M6, M8, M10)
- 50 blind rivet nuts M6, flat head, steel
- 25 blind rivet nuts M8, flat head, steel
- 25 blind rivet nuts M10, flat head, steel
- Practical case for storage and transport
- Operating instructions

### **Function:**

Diameter

Screwing and unscrewing of the RIVKLE® blind rivet nut using a knurled nut. Setting is performed through the lever ratchet function.

Technical information can be found on the last page.


Weight




M6 - M10 23530201001 1200

Article number









### **Grip range**

Defines the range of total thickness of the customers part (even if it consists of more than one layer)




## Hole geometry

If round -> diameter If hexagonal -> wigth across flats



Difference of total length before and after installation



\*in accordance to chosen RIVKLE®\*

