


**DIN 571**

**Hexagon wood screws**

Hexagon head

Stainless steel A2 | Cr(VI)-free | Wood thread



Diameter (d)	d <sub>a</sub> max.	d <sub>s</sub>		nominal size	k		e min.	s		Tool size
		min.	max.		min.	max.		min.	max.	
4	5.0	3.52	4	2.8	2.50	3.10	7.50	6.64	7	SW 7
5	6.0	4.52	5	3.5	3.13	3.88	8.63	7.64	8	SW 8
6	7.2	5.52	6	4.0	3.63	4.38	10.89	9.64	10	SW 10
7	8.2	6.42	7	5.0	4.63	5.38	13.07	11.57	12	SW 12
8	10.2	7.42	8	5.5	5.13	5.88	14.20	12.57	13	SW 13
10	12.2	9.42	10	7.0	6.55	7.45	18.72	16.57	17	SW 17
12	15.2	11.30	12	8.0	7.55	8.45	20.88	18.48	19	SW 19
16	19.2	15.30	16	10.0	9.55	10.45	26.17	23.16	24	SW 24

nominal size	Length (l)	
	min.	max.
20	18.95	21.05
25	23.95	26.05
30	28.95	31.05
35	33.75	36.25
40	38.75	41.25
45	43.75	46.25
50	48.75	51.25
60	58.50	61.50

nominal size	Length (l)	
	min.	max.
70	68.50	71.50
80	78.50	81.50
90	88.25	91.75
100	98.25	101.75
110	108.25	111.75
120	118.25	121.75
130	128.00	132.00
140	138.00	142.00

nominal size	Length (l)	
	min.	max.
150	148.00	152.00
160	158.00	162.00
180	178.00	182.00
200	197.70	202.30

All technical data refer to the measure mm



**DIN 571**

**Hexagon wood screws**

Hexagon head

Stainless steel A2 | Cr(VI)-free | Wood thread

Diameter (d)	Length (l)																				
	20	25	30	35	40	45	50	60	70	80	90	100	110	120	130	140	150	160	180	200	
4	●	●	●		●																
5		●	●	●	●	●	●														
6		●	●	●	●	●	●	●	●	●											
7					●	●	●	●													
8		●	●	●	●	●	●	●	●	●	●	●		●							
10					●		●	●	●	●	●	●	●	●	●					●	●
12							●	●	●	●	●	●	●	●							
16									●	●	●	●	●	●	●	●	●	●			

• Combinations available in the eShop | Other sizes on request

All technical data refer to the measure mm

