All technical data refer to the measure mm


RIVKLE® Standard blind rivet nuts Stainless Steel A4 | Flat head | Plain | Cylindrical | Closed


Note: RIVKLE® produced in stainless steel A4 providing the best corrosion resistance | Thread according to ISO 6h (ISO 68-1)

Technical information can be found on the last page.




Diameter	Article number	Drilling diameter d		Е	L ₂	е		Length (I)	
(d)		nominal size	В	nominal size		min.	max.	nominal size	N
M 4	23324040020	6	9	1	11.5	0.5	2	16.0	9500
M 5	23324050030	7	10	1	13.2	0.5	3	18.5	12000
M 6	23324060030	9	12	1.5	17.0	0.5	3	23.0	15000
M 8	23324080030	11	15	1.5	18.7	0.5	3	25.0	20000






Grip range

Defines the range of total thickness of the customers part (even if it consists of more than one layer)



Hole geometry

If round -> diameter
If hexagonal -> wigth across flats





in accordance to chosen RIVKLE®

