


DIN 7991 similar to ISO 10642

Countersunk bolts

Hexagon socket

Stainless steel A4 | Cr(VI)-free | Metric thread

Further information: DIN-standard has been withdrawn | due to the head geometry, these screws have only a limited load bearing capacity, see DIN EN ISO 898-1



Diameter (d)	b			da max.	dk		ds		k max.
	l up to 125	l up to 200	l longer than 200		min.	max.	min.	max.	
M3	12	–	–	3.6	5.70	6	2.86	3	1.7
M4	14	–	–	4.7	7.64	8	3.82	4	2.3
M5	16	–	–	5.7	9.65	10	4.82	5	2.8
M6	18	24	–	6.8	11.57	12	5.82	6	3.3
M8	22	28	–	9.2	15.57	16	7.78	8	4.4
M10	26	32	45	11.2	19.48	20	9.78	10	5.5
M12	30	36	49	13.7	23.48	24	11.73	12	6.5
M14	34	40	53	15.7	26.48	27	13.73	14	7.0
M16	38	44	57	17.7	29.48	30	15.73	16	7.5
M20	46	52	65	22.4	35.38	36	19.67	20	8.5

Diameter (d)	e min.	r min.	nominal size	s		Pitch (P)	t		Tool size
				min.	max.		max.	min.	
M3	2.30	0.10	2.0	2.05	2.10	0.50	1.2	0.95	SW 2
M4	2.87	0.20	2.5	2.52	2.60	0.70	1.8	1.55	SW 2,5
M5	3.44	0.20	3.0	3.02	3.10	0.80	2.3	2.05	SW 3
M6	4.58	0.25	4.0	4.02	4.12	1.00	2.5	2.25	SW 4
M8	5.72	0.40	5.0	5.02	5.14	1.25	3.5	3.20	SW 5
M10	6.86	0.40	6.0	6.02	6.14	1.50	4.4	4.10	SW 6
M12	9.15	0.60	8.0	8.02	8.18	1.75	4.6	4.30	SW 8
M14	11.43	0.60	10.0	10.02	10.18	2.00	4.8	4.50	SW 10
M16	11.43	0.60	10.0	10.02	10.18	2.00	5.3	5.00	SW 10
M20	13.72	0.80	12.0	12.03	12.21	2.50	5.9	5.60	SW 12

All technical data refer to the measure mm



DIN 7991 similar to ISO 10642

Countersunk bolts

Hexagon socket

Stainless steel A4 | Cr(VI)-free | Metric thread

nominal size	Length (l)	
	min.	max.
8	7.71	8.29
10	9.71	10.29
12	11.65	12.35
14	13.65	14.35
16	15.65	16.35
18	17.65	18.35

nominal size	Length (l)	
	min.	max.
20	19.58	20.42
25	24.58	25.42
30	29.58	30.42
35	34.50	35.50
40	39.50	40.50
45	44.50	45.50

nominal size	Length (l)	
	min.	max.
50	49.50	50.50
60	59.40	60.60
70	69.40	70.60
80	79.40	80.60
120	119.30	120.70

Diameter (d)	Length (l)																
	8	10	12	14	16	18	20	25	30	35	40	45	50	60	70	80	120
M3	●	●	●		●		●	●									
M4	●		●	●	●		●	●									
M5	●	●	●		●		●	●	●	●				●			
M6	●	●	●		●	●	●	●	●	●		●	●	●			
M8			●				●	●	●	●		●					●
M10					●		●	●		●	●	●		●			
M12							●	●	●	●	●						
M14																●	
M16											●	●		●	●		
M20											●					●	●

• Combinations available in the eShop | Other sizes on request

All technical data refer to the measure mm

