# **DIN 938**

# **Studs**


Threaded end  $\approx$  1 d

Steel 8.8 | bright | Cr(VI)-free | Metric thread



# Einschraubende

### Mutterende



Diameter		b		b <sub>1</sub>	d,	5	Pitch	z <sub>2</sub>	z <sub>1</sub>
(d)	I up to 125	I up to 200	I longer than 200	nominal size	min.	max.	(P)		
M6	18	24	-	6	5.82	6	1.00	1.25	2.5
M8	22	28	-	8	7.78	8	1.25	1.60	3.2
M10	26	32	45	10	9.78	10	1.50	1.90	3.8
M12	30	36	49	12	11.73	12	1.75	2.20	4.3
M16	38	44	57	16	15.73	16	2.00	2.50	5
M20	46	52	65	20	19.67	20	2.50	3.20	6.3
M24	54	60	73	24	23.67	24	3.00	3.80	7.5

Length (I)						
nominal size	min.	max.				
20	19.58	20.42				
25	24.58	25.42				
30	29.58	30.42				
35	34.50	35.50				
40	39.50	40.50				
45	44.50	45.50				
50	49.50	50.50				
55	54.40	55.60				

Length (I)						
min.	max.					
59.40	60.60					
64.40	65.60					
69.40	70.60					
74.40	75.60					
79.40	80.60					
84.30	85.70					
89.30	90.70					
94.30	95.70					
	min. 59.40 64.40 69.40 74.40 79.40 84.30 89.30					

Length (I)							
nominal size	min.	max.					
100	99.30	100.70					
110	109.30	110.70					
120	119.30	120.70					
130	129.20	130.80					
140	139.20	140.80					
150	149.20	150.80					


# All technical data refer to the measure mm

# **DIN 938**

# **Studs**

Threaded end  $\approx$  1 d

Steel 8.8 | bright | Cr(VI)-free | Metric thread



• Combinations available in the eShop | Other sizes on request