


## RIVKLE® Nose piece

Spare anvil for the RIVKLE® P3007 pneumatic/hydraulic setting tool for setting blind rivet nuts.

The length can be adjusted according to the RIVKLE® thread length.  
Manual adjustment, secured with a locknut.


Technical information can be found on the last page.



Diameter (d)	Article number	For tool type
M 8	23615908030	P3007
M 10	23615910030	P3007
M 12	23615912030	P3007
M 14	23615914030	P3007
M 16	23615916030	P3007

All technical data refer to the measure mm





Head diameter  
Overall length  
Thread size




**Grip range**

Defines the range of total thickness of the customers part (even if it consists of more than one layer)



**Hole geometry**

If round → diameter  
If hexagonal → width across flats



**Head projection after setting**

Variable according to the application (setting load, material substrate, etc.)

**Blind side projection after installation**

Defines the clearance needed on the blind side (cannot be used for quality control)

**Setting stroke**

Difference of total length before and after installation

**RIVKLE® Nut**



**RIVKLE® Stud**



- RIVKLE®
- Mandrel\*
- Customers part
- Anvil\*
- Counter nut
- Setting tool

\*in accordance to chosen RIVKLE®\*

All technical data refer to the measure mm

