

# RIVQUICK® Standard rivets

## Extra-large head

Note: aluminium body and steel mandrel

Technical information can be found on the last page.



Diameter (d)	Article number	d <sub>1</sub> nominal size	d <sub>2</sub> nominal size	Drilling diameter d nominal size	e	
					min.	max.
3.2	22131632080	3.2	10	3.3 - 3.4	3.0	5.0
	22131632100		10	3.3 - 3.4	5.0	7.0
	22131632120		10	3.3 - 3.4	7.0	9.0
	22131632140		10	3.3 - 3.4	9.0	11.0
	22131632160		10	3.3 - 3.4	11.0	13.0
4	22131640080	4	12	4.1 - 4.2	2.0	4.5
	22131640100		12	4.1 - 4.2	5.0	6.5
	22131640120		12	4.1 - 4.2	7.0	8.5
	22131640140		12	4.1 - 4.2	8.0	10.5
	22131640160		12	4.1 - 4.2	10.0	12.5
	22131640200		12	4.1 - 4.2	13.0	16.5
4.8	22031648100	4.8	16.5	4.9	4.0	6.0
	22031648160		16.5	4.9	10.0	12.0
	22131648100		16	4.9 - 5.0	4.5	6.0
	22131648120		16	4.9 - 5.0	5.5	8.0
	22131648140		16	4.9 - 5.0	7.5	10.0
	22131648160		16	4.9 - 5.0	9.5	12.0
	22131648180		16	4.9 - 5.0	11.5	14.0
	22131648200		16	4.9 - 5.0	13.5	16.0
	22131648240		16	4.9 - 5.0	15.5	18.0
	22131648260		16	4.9 - 5.0	17.5	20.0
	22131648300		16	4.9 - 5.0	23.5	26.0
	22131648350		16	4.9 - 5.0	25.5	31.0
	22131648400		16	4.9 - 5.0	30.5	36.0

Diameter (d)	Length (l) nominal size	Head thickness	Shear force (N)	Tensile force (N)
3.2	8	1.2	750	1000
	10	1.2	750	1000
	12	1.2	750	1000
	14	1.2	750	1000
	16	1.2	750	1000

All technical data refer to the measure mm



# RIVQUICK® Standard rivets


Extra-large head

Diameter (d)	Length (l) nominal size	Head thickness	Shear force (N)	Tensile force (N)
4	8	1.5	1200	1750
	10	1.5	1200	1750
	12	1.5	1200	1750
	14	1.5	1200	1750
	16	1.5	1200	1750
	20	1.5	1200	1750
4.8	10	2.5	1750	2300
	16	2.5	1750	2300
	10	2.0	1850	2600
	12	2.0	1850	2600
	14	2.0	1850	2600
	16	2.0	1850	2600
	18	2.0	1850	2600
	20	2.0	1850	2600
	24	2.0	1850	2600
	26	2.0	1850	2600
	30	2.0	1850	2600
	35	2.0	1850	2600
	40	2.0	1850	2600

All technical data refer to the measure mm



### Symbol list



All technical data refer to the measure mm

